

OD 8325 – OD 8525

Optical dissolve oxygen probes. 4/20 mA and RS 485 output.

These unique probes have been designed to measure dissolved oxygen based on fluorescent technology. The probes are available for submersible and in-pipe installations.

The measuring system consists of:

- optical device complete of fluorescent material,
- d.oxygen and temperature measuring circuit,
- 2-wire 4/20 mA analog output,
- RS 485 digital output,
- nozzle for the autoclean by external pressure air (OD 8325).

The measuring is provided in ppm or % of air with automatic temperature compensation.

Through commands from the Personal Computer hyperterminal, the serial interface allows the d.oxygen and temperature data transmission, the ppm or % of air scale selection, the configuration of pressure, salinity and R.H compensation, the zero and sensitivity calibration.

Thanks to its 4/20 mA isolated output, the probe can be directly connected to a PLC or data logger.

The probe can be connected to B&C Electronics controller BC 7335, BC 7635, BC 7635.010, BC 7687 or BC 6587, which provide the power, the measuring readout, 2 set-points, alarm relay and the holding function for an external cleaning cycle.

The most common applications of this probe include: water quality monitoring, municipal and industrial water treatment and aquaculture.

Principle of operation

A light beam of a specific wavelength is sent to a special fluorescent layer in contact with the sample.

The absorbed light energy is partially released as a light pulse with an higher wavelength.

This phenomenon is called fluorescence.

If oxygen molecules are in contact with the sensing layer, the fluorescing is reduced (quenching).

By measuring the amount of quenching it is possible to determine the oxygen concentration.

Архангельск (8182)63-90-72
Астана +7(7172)727-132
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Казань (843)206-01-48

Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41



OD 8325

OD 8525

Technical specifications

| | |
|---------------------------|--|
| Scale: | 0/20 ppm - 0/200 % air |
| Sensitivity: | ± 0,5 % of the scale |
| Response time: | 95% in < 60 seconds |
| Power supply: | 9/36Vdc |
| Analog output: | 4/20 mA isolated current Loop |
| Load: | 600 Ω max. at 24Vdc |
| Digital output: | RS 485 |
| Temperature compensation: | automatic |
| Secondary parameters: | pressure, salinity, RH |
| Room temperature: | -5/50 °C |
| Max. pressure: | 1 bar at 25 °C (OD 8325); 6 bar at 25 °C (OD 8525) |
| Autoclean: | by pressure air 3 bar max (OD 8325) |
| Dimensions OD 8325: | L=165 mm total, D= 60 mm |
| Dimensions OD 8525: | L=143 mm total, D= 40 mm |
| Body: | PVC |
| Cable: | 10 m (100 m max.) |
| Protection: | IP 68 |

The technical specifications may be changed without notice

Accessories

| | |
|---------|--|
| BC 8701 | RS485/USB converter for power supply through PC connection |
| OD 8391 | Optical sensing element replacement kit |

Accessories for OD 8325

| | |
|-------------|-----------------------------------|
| 0012.450043 | Extension pipe adapter |
| 0012.000624 | Swivel mounting + 0012.450043 |
| 0012.440040 | 33 m PVC tubing for pressured air |

Accessories for OD 8525

| | |
|------------|--|
| TU 910 | Overflow cell |
| YAT75M0021 | Flow Tee assembly for in-pipe installation |

Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78

Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Turbidity probes. 4/20 mA and RS 485 output.

These unique probes have been designed to measure turbidity based on nephelometric method (ISO 7027 – EN 27027). The probes are available for submersible and in-pipe installations.

The measuring system consists of:

- Infrared light source,
- 90 degree scattered light detector,
- Detector of the clean lens status,
- 2-wire 4/20 mA analog output,
- RS 485 digital output
- Nozzle for the autoclean by external pressured air (TU 8325).

Through commands from the Personal Computer hyperterminal, the serial interface allows the measuring and check signals transmission, the scale selection, the analog or digital operating mode selection, the zero and sensitivity calibration.

Thanks to its 4/20 mA isolated output, the probe can be directly connected to a PLC or data logger, and configured in NTU, g/l, % or other.

The probe can be connected to B&C Electronics controller BC 7335, BC 7635, BC 7635.010, BC 7687 or BC 6587, which provide the power, the measuring readout, 2 set-points, the alarm relay and the holding function for an external cleaning cycle.

The most common applications of this probe include: water quality monitoring, municipal and industrial water treatment and aquaculture.

Principle of operation

The turbidity follows the back nephelometric method (ISO 7027 – EN 27027).

A light beam is sent to the sample through an optical lens.

The 90 degree scattered light by suspended particle is collected by the probe through a second lens and it is converted in an electric signal proportional to the turbidity of the sample.

The probe uses an infrared light and the measuring is not affected by the color of the sample.



Technical specifications

Scale: 0/4,000 – 0/40,00 – 0/400,0 NTU

Sensitivity NTU: 70/130 %

Zero NTU: ± 0,400 NTU all scales

Power supply: 9/36Vdc

Analog output: 4/20 mA isolated current Loop

Load: 600 Ω max. at 24Vdc

Digital output: RS 485

Room temperature: -5/50 °C

Max. pressure: 1 bar at 25 °C (TU 8325); 6 bar at 25 °C (TU 8525)

Autoclean: by pressure air 3 bar max (TU 8325)

Dimensions TU 8325: L=165 mm total, D= 60 mm

Dimensions TU 8525: L=143 mm total, D= 40 mm

Body: PVC

Cable: 10 m (100 m max.)

Protection: IP 68

The technical specifications may be changed without notice

Accessories

BC 8701 RS485/USB converter for power supply though PC connection

Accessories for TU 8325

0012.450043 Extension pipe adapter

0012.000624 Swivel mounting + 0012.450043

0012.440040 33 m PVC tubing for pressured air

Accessories for TU 8525

TU 910 Overflow cell

YAT75M0021 Flow Tee assembly for in-pipe installation

High turbidity and suspended solids probes. 4/20 mA and RS 485 output.

These unique probes have been designed to measure to measure high turbidity and suspended solids based on back scattering technology.

The probes are available for submersible and in-pipe installations.

The measuring system consists of:

- Infrared light source,
- Detector of scattered light by suspended particles,
- Detector of the clean lens status,
- 2-wire 4/20 mA analog output,
- RS 485 digital output
- Nozzle for the autoclean by external pressured air (TU 8355).

Through commands from the Personal Computer hyperterminal, the serial interface allows the measuring and check signals transmission, the scale selection, the analog or digital operating mode selection, the zero and sensitivity calibration.

Thanks to its 4/20 mA isolated output, the probe can be directly connected to a PLC or data logger, and configured in FTU, g/l, % or other.

The probe can be connected to B&C Electronics controller BC7335, BC 7635, BC 7635.010, BC 7687 or BC 6587, which provide the power, the measuring readout, 2 set-points, the alarm relay and the holding function for an external cleaning cycle.

The most common applications of this probe include: water quality monitoring, municipal and industrial water treatment and aquaculture.

Principle of operation

The turbidity and suspended solid measurement follows the back scattering method.

A light beam is sent in the sample through an optical lens.

The back scattered light by suspended particle is collected by the probe through a second lens, detected and converted in an electric signal proportional to the turbidity of the sample.

The probe uses an infrared light and the measuring is not affected by the color of the sample.

Архангельск (8182)63-90-72
Астана +7(7172)727-132
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Казань (843)206-01-48

Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81
Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41



TU 8355

TU 8555

Technical Specifications

| | |
|----------------------------|--|
| Scale: | 0/100 – 0/1000 – 0/10000 FTU |
| Sensitivity FTU: | 70/130 % |
| Zero FTU: | ± 10 FTU all scales |
| Power supply: | 9/36Vdc |
| Analog output: | 4/20 mA isolated current Loop |
| Load: | 600 Ω max. at 24Vdc |
| Digital output: | RS 485 |
| Room temperature: | -5/50 °C |
| Max. pressure: | 1 bar at 25 °C (TU 8355); 6 bar at 25 °C (TU 8555) |
| Autoclean: | by pressure air 3 bar max (TU 8355) |
| Dimensions TU 8355: | L=165 mm total, D= 60 mm |
| Dimensions TU 8555: | L=143 mm total, D= 40 mm |
| Body: | PVC |
| Cable: | 10 m (100 m max.) |
| Protection: | IP 68 |

The technical specifications may be changed without notice

Accessories

BC 8701 RS485/USB converter for power supply though PC connection

Accessories for TU 8355

0012.450043 Extension pipe adapter
0012.000624 Swivel mounting + 0012.450043
0012.440040 33 m PVC tubing for pressured air

Accessories for TU 8555

TU 910 Overflow cell
YAT75M0021 FlowTee assembly for in-pipe installation

Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78

Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93